

BeMicron®

Intuitive

Donned without touching the outside of the coverall

Safety

Remove any risk of contamination during the gowning procedure

Economical

Reduce your costs whilst increasing your productivity and quality

Sustainable

All products are reusable



BeMicron® Original

Coverall with integrated open hood

 30 sec

ESD

Grades **A,B,C,D**

ISO **3 → 7**

BeMicron Original can be used in almost all cleanrooms classes.

Made from a fabric carefully selected for its quality, performance and lasting reliability, it offers excellent mechanical strength and protects against contamination. It has a perfectly-smooth technical filtering wall, at both front and back, and constitutes a veritable barrier against human contamination. Thanks to the BeMicron® folding system and donning procedure, the operator's movements follow each other automatically without need to touch the outside of the coverall and without errors in procedure.

The doning procedure



1

Out of the bag



2

White = left
Red = right



3

Easy gowning
system



4

Easely
adjustable



5

Zipper quickly
closed

30 sec



BeMicron®

Intuitive

Donned without touching the outside of the coverall

Safety

Remove any risk of contamination during the gowning procedure

Economical

Reduce your costs whilst increasing your productivity and quality

Sustainable

All products are reusable

BeMicron® Original



A hood that fits perfectly

Adjustable both vertically and horizontally with studs, the hood completely encloses the head, providing full protection with excellent comfort.



The hood adapts to all requirements.

Whether or not a disposable mask is required, our hood adapts and is available with or without a mask. The masked hood perfectly covers the nose. A soft and light fabric placed inside the mask ensures maximum comfort.



Durable and effective cuff

The cuff or stud finish allows the sleeves to fit perfectly into gloves. The cuff is made of antistatic polyester and is resistant to various sterilization processes. The studs are made of stainless steel.



Protective clothing with optimum comfort

The elastic in the back ensures the BeMicron adjusts perfectly to the body to prevent any «blow-up effect» caused by movements in the body.



Gowning without touching the coverall

The BeMicron is unique in the fact that the outside of the garment is protected from any risk of contact contamination (hand and surface). The base of the zip is already engaged and in place reducing contact time.. Simply use the grip to close the zip.



Boots fixed to the legs of the coverall

Studs on the coverall's leg allow boots to be fixed in a fully protective way. We also supply boots with anti-slip soles which are resistant to the various sterilization cycles. The boots conform to standard EN 344 because of their antistatic qualities.

